

**Signal tower Modlight70 Pro equipped with LED modules**

blue,green,amber,red,buzzer

Basis, buzzer, LED modules  
red, yellow, green, blue**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27371230      |
| ECLASS-6.1              | 27371230      |
| ECLASS-7.0              | 27371230      |
| ECLASS-8.0              | 27371230      |
| ECLASS-9.0              | 27371230      |
| ECLASS-10.1             | 27371230      |
| ECLASS-11.1             | 27371230      |
| ECLASS-12.0             | 27371230      |
| ETIM-5.0                | EC001042      |
| GTIN                    | 4048879759915 |
| Gümrük tarife no (gtip) | 85318070      |
| Paket miktarı           | 1             |

**Electrical data | Supply**

|                           |        |
|---------------------------|--------|
| Operating voltage DC      | 24 V   |
| Operating voltage DC min. | 21,6 V |
| Operating voltage DC max. | 26,4 V |
| Current consumption max.  | 430 mA |

**Industrial communication | HMI**

|                               |                                                       |
|-------------------------------|-------------------------------------------------------|
| Buzzer sound                  | fast beep, continuous beep, fast high-low, sweep tone |
| Reduced sound pressure at 1 m | 80 dB                                                 |
| Sound pressure at 1 m         | 90 dB                                                 |

**Device protection | Electrical**

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.  
Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmalî sınırlıdır. Sürüm: 2024-04-25

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

|                                                 |                  |
|-------------------------------------------------|------------------|
| Degree of protection (EN IEC 60529)             | IP65             |
| Additional condition protection degree          | inserted, locked |
| <b>Mechanical data   Material data</b>          |                  |
| Color housing                                   | black            |
| Material housing                                | Plastic          |
| <b>Mechanical data   Mounting data</b>          |                  |
| Height                                          | 334 mm           |
| Width                                           | 70 mm            |
| Depth                                           | 70 mm            |
| <b>Environmental characteristics   Climatic</b> |                  |
| Operating temperature min.                      | -30 °C           |
| Operating temperature max.                      | 60 °C            |