


Signal tower Modlight70 Pro equipped with LED modules

green,amber,red,M12 plug side

Basic + LED modules + M12 (side)
green, yellow, red**Ürün Linki****örnekleme**

Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-8.0	27371230
ECLASS-9.0	27371230
ECLASS-10.1	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ETIM-5.0	EC001042
GTIN	4048879759946
Gümrük tarife no (gtip)	85318070
Paket miktarı	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	135 mA

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Color housing	black
---------------	-------

Material housing Plastic

Mechanical data | Mounting data

Height	293 mm
Width	70 mm
Depth	70 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	60 °C