MURR ELEKTRONIK
stay connected

Signal tower Modlight70 Pro equipped with LED modules

green,amber,red,buzzer,M12 plug side

Basic, buzzer, flash + LED modules + M12 (side)
green, yellow, red

Ürün Linki

örnekleme

Ürün Image farklı olabilir



PIN 1: +
PIN 2: LED (red)
PIN 3: –
PIN 4: LED (clear)
PIN 5: LED (yellow)
PIN 6: LED (blue)
PIN 7: LED (green)
PIN 8: Continious alarm

Ticari bilgiler	
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-8.0	27371230
ECLASS-9.0	27371230
ECLASS-10.1	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ETIM-5.0	EC001042
GTIN	4048879759953
Gümrük tarife no (gtip)	85318070
Paket miktarı	1

Electrical data | Supply	
Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	385 mA

Industrial communication | HMI	
Buzzer sound	fast beep, continuous beep, fast high-low, sweep tone
Reduced sound pressure at 1 m	80 dB
Sound pressure at 1 m	90 dB

HMI | Illumination properties

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Blink cycles	60 ±12 per minute
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked
Mechanical data | Material data	
Color housing	black
Material housing	Plastic
Mechanical data | Mounting data	
Height	293 mm
Width	70 mm
Depth	70 mm
Environmental characteristics | Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	60 °C

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.
Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmali sınırlıdır. Sürüm: 2024-04-25