

M12 female 0° A-cod. screw terminal4-pol., 0,14 - 1,5mm², 2,5 - 8mm

Female straight

M12, 4-pole



Screw terminals

Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.

Ürün Linki

örnekleme



Ürün Image farklı olabilir

**Side 1**

Degree of protection (EN IEC 60529)

IP67

Ticari bilgiler

ECLASS-6.0 27279221

ECLASS-7.0 27440104

ECLASS-8.0 27440104

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.

Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmalî sınırlıdır. Sürüm: 2024-04-20

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

ECLASS-9.0	27440102
ECLASS-10.1	27440102
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ETIM-5.0	EC001855
GTIN	4048879838887
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

Electrical data | Supply

Operating voltage AC max.	250 V
Operating voltage DC max.	250 V
Operating current per contact max. (40°C)	7,5 A

Installation

Connection cross section min.	0,14 mm ²
Connection cross section max.	1,5 mm ²

Installation | Connection

Tightening torque	0,6 Nm
Mating cycles min.	100

Device protection | Electrical

Additional condition protection degree	screwed, mounted
Pollution Degree	3/2
Insulation resistance min.	100 MΩ

Mechanical data | Mounting data

Mounting method	Schraubgewinde
Clamping range min.	2,5 mm
Clamping range max.	8 mm
Height	57 mm
Width	20 mm
Depth	20 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	85 °C