

Adapter M12 male/ female B-cod./ D-Sub 9-pol. 180°

Shielded, 12Mbit/s

PROFIBUS

Bus connection plug 180°

SUB-D9 (male); M12× 1 mm, B-coded

Ürün Linki**örnekleme**

Ürün Image farklı olabilir

Ticari bilgiler

ECLASS-6.0	27061801
ECLASS-7.0	27061801
ECLASS-8.0	27061801
ECLASS-9.0	27061801
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC001855
GTIN	4048879303644
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

Electrical data

Terminating resistor	connectable, integrated
----------------------	-------------------------

Electrical data | Supply

Operating voltage DC min.	4,75 V
Operating voltage DC max.	5,25 V
Current consumption max.	12,5 mA

Industrial communication

Data transmission rate max.	12 MBit/s
-----------------------------	-----------

Installation | Connection

Family construction form	M12
--------------------------	-----

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP30
-------------------------------------	------

Mechanical data | Mounting data

Height	77 mm
Width	31 mm
Depth	15 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	70 °C
Important installation notes	
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.