

SCRJ POF male 0° crimp connection

2-pol., POF 1mm, 6,5 - 9,5mm

Push Pull SCRJ POF male, field-wireable

Connection

Crimp

1 mm

AIDA conform

The resistance to aggressive media should be individually tested for your application. Further details on request.

Ürün Linki**örnekleme**

Ürün Image farklı olabilir

Ticari bilgiler

ECLASS-6.0	27279220
ECLASS-7.0	27440103
ECLASS-8.0	27440103
ECLASS-9.0	27440103
ECLASS-10.1	27440101
ECLASS-11.1	27440101
ECLASS-12.0	27440114
ETIM-5.0	EC002635
GTIN	4048879603652
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

InstallationConnection cross section max. 1 mm²**Installation | Connection**

Connection	Crimp
Family construction form	SCRJ
Gender	male

Device protection | Electrical

Degree of protection (EN IEC 60529) IP20

Mechanical data | Mounting data

Mounting method Push Pull

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	70 °C