

Velcro base including velcro for ITEM-profiles

Clamping range 4-20mm, width 10mm, length 150mm

Simple, tool-free mounting in common aluminium profiles
45° rotation allows cable fastening across or parallel to the profile

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Ticari bilgiler

ECLASS-6.0	27279221
ECLASS-7.0	27140706
ECLASS-8.0	27140706
ECLASS-9.0	27140706
ECLASS-10.1	27140706
ECLASS-11.1	27140706

ECLASS-12.0	27140706
ETIM-5.0	EC002635
GTIN	4065909080641
Gümrük tarife no (gtip)	63079098
Paket miktarı	10
Mechanical data Material data	
Combustibility class (UL94)	V-0
Material housing	PA
Mechanical data Mounting data	
Clamping range min.	4 mm
Clamping range max.	20 mm
Width	10 mm