

M12 Power male 0° L-cod. IDC5-pol., 0,75 - 1,5mm², 5,8 - 13,5mm, shielded

Male straight

M12, 5-pole

L-coded

Field-wireable

IDC terminals

0.75...1.5 mm²




Sealing range (cable Ø)

5.8...13.5 mm

The resistance to aggressive media should be individually tested for your application. Further details on request.

Ürün Linki

örnekleme



Ürün Image farklı olabilir

Side 1

Family construction form M12P

Coding L

Ticari bilgiler

ECLASS-6.0 27279221

ECLASS-7.0 27440104

ECLASS-8.0 27440104

ECLASS-9.0	27440102
ECLASS-10.1	27440102
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ETIM-5.0	EC001855
GTIN	4048879682541
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

Electrical data | Supply

Operating voltage DC max.	63 V
Current operating per contact max.	12 A

Installation

Connection cross section max.	1,5 mm ²
-------------------------------	---------------------

Installation | Connection

Tightening torque	0,6 Nm
Mounting set	M12 x 1
Width across flats	SW17
Mating cycles min.	500

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65, IP67
Additional condition protection degree	inserted, screwed

Mechanical data

Contour for corrugated hose	without
-----------------------------	---------

Mechanical data | Material data

Coating housing	Nickeled
Coating contact	gold plated
Material housing	Zinc die-casting
Material contact carrier	PA

Mechanical data | Mounting data

Mounting method	inserted, screwed, Shaking protection
Clamping range min.	5,8 mm
Clamping range max.	13,5 mm

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	85 °C