

RJ45 module - female

Female


RJ45

Technical data will be only guaranteed with Murrelektronik components.


The clip 70MH-ZZ100-0000000 is needed (2x)

Ürün Linki

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27143424
ECLASS-6.1	27261204
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000437
GTIN	4048879664066
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

Electrical data | Supply

Operating voltage AC	50 V
Operating voltage DC	50 V

Industrial communication

Transfer parameters	CAT6A (IEC 60512-27-100:2008, TIA-568-C.2:2009)
---------------------	---

Installation | Connection

Gender	female
Mating cycles min.	500

Device protection | Electrical

Pollution Degree	3
Rated surge voltage	0,8 kV
Overvoltage category (EN 60950-1)	III
Mechanical data Material data	
Coating contact	gold plated
Combustibility class (UL94)	V-0
Material housing	PC
Material contact	Cu
Mechanical data Mounting data	
Number of module slots	1
Height	41 mm
Width	34,1 mm
Depth	14,6 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	70 °C