

Pneumatic insert - male, 3 mm

Pneumatic male

Internal hose Ø

3 mm

Technical data will be only guaranteed with Murrelektronik components.

Ürün Linki**örnekleme**

Ürün Image farklı olabilir

Ticari bilgiler

ECLASS-6.0	27261204
ECLASS-6.1	27261290
ECLASS-7.0	27440290
ECLASS-8.0	27440290
ECLASS-9.0	27440220
ECLASS-10.1	27440220
ECLASS-11.1	27440220
ECLASS-12.0	27440220
ETIM-5.0	EC000438
GTIN	4048879672757
Gümrük tarife no (gtip)	39269097
Paket miktarı	10

Installation | Connection

Gender	male
Mating cycles min.	500

Mechanical data

Operating pressure max.	8 bar
Integrated valve	no

Mechanical data | Material data

Material housing	Delrin Acetal
------------------	---------------

Mechanical data | Mounting data

Internal hose Ø	3 mm
-----------------	------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	80 °C

