

**Pneumatic insert - female, 4 mm**

Pneumatic female

Internal hose Ø

4 mm

Technical data will be only guaranteed with Murrelektronik components.

**Ürün Linki****örnekleme**

Ürün Image farklı olabilir

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27261204      |
| ECLASS-6.1              | 27261290      |
| ECLASS-7.0              | 27440290      |
| ECLASS-8.0              | 27440290      |
| ECLASS-9.0              | 27440220      |
| ECLASS-10.1             | 27440220      |
| ECLASS-11.1             | 27440220      |
| ECLASS-12.0             | 27440220      |
| ETIM-5.0                | EC000438      |
| GTIN                    | 4048879672801 |
| Gümrük tarife no (gtip) | 39269097      |
| Paket miktarı           | 10            |

**Installation | Connection**

|                    |        |
|--------------------|--------|
| Gender             | female |
| Mating cycles min. | 500    |

**Mechanical data**

|                         |       |
|-------------------------|-------|
| Operating pressure max. | 8 bar |
| Integrated valve        | no    |

**Mechanical data | Material data**

|                  |               |
|------------------|---------------|
| Material housing | Delrin Acetal |
|------------------|---------------|

**Mechanical data | Mounting data**

|                 |      |
|-----------------|------|
| Internal hose Ø | 4 mm |
|-----------------|------|

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -40 °C |
| Operating temperature max. | 80 °C  |

