

MODL. VARIO 6-way coupling housing type B

nickel plated aluminum

Mobile housing (round)
Aluminium
6-way**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

Ticari bilgiler

ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
GTIN	4048879573009
Gümrük tarife no (gtip)	85389099
Paket miktarı	1

Mechanical data

Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar

Mechanical data | Material data

Coating housing	nickel plated
Material housing	Aluminium

Mechanical data | Mounting data

Looking techniques	Clip locking
--------------------	--------------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	120 °C