

**MODL. VARIO 8-way coupling housing type B**

stainless steel type 1.4404 (V4A)

Mobile housing  
Stainless steel 1.4404 (V4A)  
8-way

**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27260702      |
| ECLASS-6.1              | 27260708      |
| ECLASS-7.0              | 27440312      |
| ECLASS-8.0              | 27440312      |
| ECLASS-9.0              | 27440312      |
| ECLASS-10.1             | 27440312      |
| ECLASS-11.1             | 27440312      |
| ECLASS-12.0             | 27440312      |
| ETIM-5.0                | EC002641      |
| GTIN                    | 4048879573153 |
| Gümrük tarife no (gtip) | 85389099      |
| Paket miktarı           | 1             |

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP65, IP67, IP68  |
| Degree of protection (ISO 20653:2013)  | IP66K, IP69K      |
| Additional condition protection degree | inserted, screwed |

**Mechanical data | Material data**

|                  |                              |
|------------------|------------------------------|
| Material housing | Stainless steel 1.4404 (V4A) |
|------------------|------------------------------|

**Mechanical data | Mounting data**

|                 |              |
|-----------------|--------------|
| Mounting method | screw fixing |
|-----------------|--------------|

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -20 °C |
| Operating temperature max. | 120 °C |