

VALVE PLUG SUPPRESSOR FORM A - 18MM

RC and LED, 48VAC/DC/30VA/W



48 V AC/DC

RC + LED

Remove plug gasket when fitting adapter. Other LED colors on request.

Ürün Linki

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-8.0	27371013
ECLASS-9.0	27371013
ECLASS-10.1	27371013

ECLASS-11.1	27371013
ECLASS-12.0	27371013
ETIM-5.0	EC000197
GTIN	4048879012126
Gümrük tarife no (gtip)	85363010
Paket miktarı	1
Electrical data	
Capacity CX	20 ms
Holding power max.	30 W
Electrical data Supply	
Cut-off peak voltage max.	90 V
Electrical data Input	
Input voltage AC min.	24 V
Input voltage AC max.	53 V
Input voltage DC min.	24 V
Input voltage DC max.	53 V
Diagnostics	
Status indication LED	yellow
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Coating contact	silver-plated
Color housing	black
Material housing	PA
Material contact	Bronze
Mechanical data Mounting data	
Height	37 mm
Width	53 mm
Depth	33 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Housing temperature max. (EN 61347-2-13)	130 °C