

MOTOR SUPPRESSOR

RC, 3x400VAC/4kW

3× 400 V AC

RC

Suppressors for other voltages, frequencies, and motor ratings available on request. Do not use RC motor suppressors with frequency inverters.

Link to Product

Illustration



Product may differ from Image



| 取引条件        |          |
|-------------|----------|
| ECLASS-6.0  | 27371013 |
| ECLASS-6.1  | 27371013 |
| ECLASS-7.0  | 27371013 |
| ECLASS-8.0  | 27371013 |
| ECLASS-9.0  | 27371013 |
| ECLASS-10.1 | 27371013 |

|                                          |                   |
|------------------------------------------|-------------------|
| ECLASS-11.1                              | 27371013          |
| ECLASS-12.0                              | 27371013          |
| ETIM-5.0                                 | EC000197          |
| GTIN                                     | 4048879019620     |
| HSコード                                    | 85363010          |
| Packaging unit                           | 1                 |
| Electrical data   Supply                 |                   |
| Power frequency                          | 50 ... 60 Hz      |
| Electrical data   Input                  |                   |
| Input voltage AC                         | 400 V             |
| Installation                             |                   |
| Connection cross-section solid min.      | 0,75 mm²          |
| Connection cross-section solid max.      | 2,5 mm²           |
| Installation   Connection                |                   |
| Connection information                   | terminal          |
| Family construction form                 | M4                |
| Installation   Pin assignment            |                   |
| No. of poles                             | 3                 |
| Device protection   Media                |                   |
| Flame resistance                         | flame retardant   |
| Mechanical data   Material data          |                   |
| Combustibility class housing (UL94)      | V-0               |
| Material housing                         | Plastic           |
| Material potting compound                | 2-component epoxy |
| Mechanical data   Mounting data          |                   |
| Height                                   | 75 mm             |
| Width                                    | 45 mm             |
| Depth                                    | 42 mm             |
| Environmental characteristics   Climatic |                   |
| Operating temperature min.               | -20 °C            |
| Operating temperature max.               | 60 °C             |