



LUGS 32 FOR SIGNAL TRANSFER

250V / 8 A

32-pole
Screw plug-in terminals

[Link to Product](#)

Illustration



Product may differ from Image

取引条件	
ECLASS-6.0	27143424
ECLASS-6.1	27260708
ECLASS-7.0	27141152
ECLASS-8.0	27141152
ECLASS-9.0	27141152
ECLASS-10.1	27141152
ECLASS-11.1	27141152
ECLASS-12.0	27141152
ETIM-5.0	EC001283
GTIN	4048879026260
HSコード	85369010
Packaging unit	1

Electrical data Supply	
Operating voltage AC	250 V
Operating current max.	8 A
Installation	
Connection cross-section solid max.	4 mm ²
Installation Connection	
Connection	Screw terminals SK
Device protection Electrical	
Overvoltage category (EN 60664-1)	I
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	75 mm
Width	90 mm
Depth	66 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C