

PROFIBUS-PLUG-MALE (SUB-D) 90°

Cut clamp for rigid and flexible wires

Bus connection plug 90°
PROFIBUS
SUB-D9 (male), IDC terminals, rigid and flexible cable, programming device connection
PROFIBUS, FC cable rigid/flexible, 1× 2× 0.64 mm², for outer diameter 8.0 ±0.5 mm

Link to Product

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC001855
GTIN	4048879050562
HSコード	85389091
Packaging unit	1
Electrical data	
Terminating resistor	connectable, integrated
Electrical data Supply	
Operating voltage DC min.	4,75 V
Operating voltage DC max.	5,25 V
Current consumption max.	12,5 mA
Industrial communication	
Data transmission rate max.	12 MBit/s
Installation Connection	

Connection

Cut clamps IDC

Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Pollution Degree	2
Mechanical data Mounting data	
Height	72 mm
Width	40 mm
Depth	17 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	80 °C