

CAN-PLUG-MALE (SUB-D) 90°

Screw terminals up to 1Mbps/s

Bus connection plug 90°  
SUB-D9 (female), screw terminals  
max. 1 Mbit/s with switchable terminal resistors  
CANopen  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

| 取引条件                                |                         |
|-------------------------------------|-------------------------|
| ECLASS-6.0                          | 27279221                |
| ECLASS-7.0                          | 27440104                |
| ECLASS-8.0                          | 27440104                |
| ECLASS-9.0                          | 27440102                |
| ECLASS-10.1                         | 27242692                |
| ECLASS-11.1                         | 27242692                |
| ECLASS-12.0                         | 27242692                |
| ETIM-5.0                            | EC002584                |
| GTIN                                | 4048879049825           |
| HSコード                               | 85366990                |
| Packaging unit                      | 1                       |
| Electrical data                     |                         |
| Terminating resistor                | connectable, integrated |
| Industrial communication            |                         |
| Data transmission rate max.         | 1 MBit/s                |
| Installation                        |                         |
| Connection cross section max.       | 1 mm²                   |
| Device protection   Electrical      |                         |
| Degree of protection (EN IEC 60529) | IP20                    |
| Mechanical data   Mounting data     |                         |
| Height                              | 65 mm                   |

|                                          |                    |
|------------------------------------------|--------------------|
| Width                                    | 48 mm              |
| Depth                                    | 16 mm              |
| Environmental characteristics   Climatic |                    |
| Operating temperature min.               | 0 °C               |
| Operating temperature max.               | 60 °C              |
| Storage temperature min.                 | -25 °C             |
| Storage temperature max.                 | 80 °C              |
| Connection type 2                        |                    |
| Family construction form                 | D-Sub              |
| Gender                                   | female             |
| No. of poles                             | 9                  |
| PIN 2                                    | CAN_L              |
| PIN 3                                    | CAN_GND            |
| PIN 5                                    | CAN_SHLD           |
| PIN 6                                    | 0 V                |
| PIN 7                                    | CAN_H              |
| PIN 9                                    | CAN V +            |
| Connection                               | Screw terminals SK |
| Family construction form                 | terminal           |
| Gender                                   | female             |
| No. of poles                             | 6                  |