

Product discontinued until 31.10.2018, replaced by: 56469

Gateway Ethernet-IP/AS-i, 1 Master, Spec. 3.0, IP20

Gateway-Singlemaster

via pluggable spring clamp plug-in terminals on the front 0.5...1.5 mm²

AS-Interface/EtherNet/IP

Specification 3.0

Current manuals, GSD/type data can be downloaded at: www.murrelektronik.com



Other gateways on request.

Link to Product

Illustration



Product may differ from Image



取引条件

ECLASS-6.0	27242208
ECLASS-7.0	27242208
ECLASS-8.0	27242208
ECLASS-9.0	27242208
ETIM-5.0	EC001604
GTIN	4048879495707
HSコード	85176200
Packaging unit	1

Electrical data

Rated operating current AS-Interface max.	200 mA
---	--------

Electrical data | Supply

Operating voltage DC	30 V
----------------------	------

Industrial communication

Supported protocol	EtherNet/IP
--------------------	-------------

Industrial communication | AS-Interface

AS-i specification	V3.0
Number of slaves max.	62
Diagnostic interface serial	RJ45/Fieldbus or PS2/RS232

このデータシートに含まれる情報は最大限の注意を払って作成されました。

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-05-06

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Cycle time AS-i150 μs × (number of slaves + 2)

Installation | Connection

Family construction formRJ45

Device protection | Electrical

Degree of protection (EN IEC 60529)IP20

Rated insulation voltage500 V

Mechanical data | Mounting data

Mounting methodgeschnappt

Suitable for mounting typemounting rail, (EN 60715)

Height120 mm

Width85 mm

Depth83 mm

Environmental characteristics | Climatic

Operating temperature min.0 °C

Operating temperature max.55 °C

Storage temperature min.-25 °C

Storage temperature max.85 °C

Conformity

Low Voltage DirectiveEN 50295