




Reset button with 2 illuminated push buttons

Every 1 NO contact in a IP65 enclosure

R-Button / 42 2NO L M12(8)
with M12 connection
8-pole
2 buttons can be lit (each 1 NO contact)
Delivery contents:
Flat lens, transparent clear, red, yellow, green, blue
Label plates, O, I, R, ↑, ↓
mounting with clip on the back side

Link to Product

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27371228
ECLASS-6.1	27371228

ECLASS-7.0	27371228
ECLASS-8.0	27371228
ECLASS-9.0	27371228
ECLASS-10.1	27371228
ECLASS-11.1	27371228
ECLASS-12.0	27371228
ETIM-5.0	EC000225
GTIN	4048879594325
HSコード	85365080
Packaging unit	1

Electrical data

Operating voltage AC/DC LED illumination max.	30 V
Operating current LED illumination	14 mA @24 V DC

Electrical data | Supply

Operating voltage DC min.	1 V
Operating voltage DC max.	36 V
Operating voltage DC (UL Recognized)	30 V
Operating current	1,5 A

Device protection

Condition lifetime	load-dependent, temperature dependent
--------------------	---------------------------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	1000000 Cycles

Device protection | Mechanical

Mechanical endurance	1000000 Cycles
----------------------	----------------

Mechanical data

Bounce time max.	10 ms
------------------	-------

Mechanical data | Material data

Material contact	AgNi
------------------	------

Mechanical data | Mounting data

Height	29 mm
Width	124 mm
Depth	42 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C

Connection type 1

Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	8
PIN 1	NO 1
PIN 2	NO 1
PIN 3	X 2 -
PIN 4	X 1 +
PIN 5	NO 2

PIN 6	NO 2
PIN 7	X 2 -
PIN 8	X 1 +