



MPS POWER SUPPLY 3-PHASE,

IN: 360-550VAC OUT: 22-28V/20ADC

INPUT: 3× 360...550 V AC
OUTPUT: 22...28 V DC
Current: 20 A
Protection IP20
Wide voltage input
Units decoupling through diode block at parallel usage.
additional mounting feet for screw mounting part no. 89500

Link to Product

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002

ECLASS-9.0	27040701
ETIM-5.0	EC002540
GTIN	4048879080606
HSコード	85044083
Packaging unit	1
Electrical data	
Parallel connection	yes
Series connection	yes
Security level	SELV
Electrical data Supply	
Power frequency	50 ... 60 Hz
Electrical data Input	
Input voltage AC min.	360 V
Input voltage AC max.	550 V
Input current AC (3-phase)	0,84 A
External back-up fuse per phase max.	10 A
Phase number input	3
Efficiency	90 %
Electrical data Output	
Output voltage DC	24 V
Output voltage DC min.	22 V
Output voltage DC max.	28 V
Output voltage adjustable	yes
Output current	20 A
Output current (UL)	24 A
Mains failure bridging min.	3 ms @ 400 V AC
Phase monitoring	Switching off during 2-phase operation
Ripple effective max.	20 mV
Spikes (s-s) max.	100 mV
Device protection Electrical	
Overload protection output	yes
Short-circuit protection output	yes
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	132 mm
Width	243 mm
Depth	123 mm
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Relative humidity min. (operation)	30 %
Relative humidity max. (operation)	90 % no condensation
Connection type 3	
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green

No. of poles	2
PIN 1	Signal
PIN 2	Signal +
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	PE
PIN 2	L 1
PIN 3	L 2
PIN 4	L 3
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	+
PIN 2	+
PIN 3	-
PIN 4	-