



MB CAP ULTRA BUFFER MODUL

IN: 20,4-26,4VDC OUT:23VDC/3A for max.1A/21S

INPUT: 24 V DC (SELV/PELV)
OUTPUT: max. 3 A
7 s (3 A); 21 s (1 A)

[Link to Product](#)

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27049190
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040705
ECLASS-10.1	27040705

ECLASS-11.1	27040705
ECLASS-12.0	27040705
ETIM-5.0	EC002584
GTIN	4048879079808
HSコード	85322900
Packaging unit	1
Electrical data	
Security level	SELV/PELV
Electrical data Input	
Input voltage DC min.	20,4 V
Input voltage DC max.	26,4 V
Current input AC	3 A
Charging time min.	25 s
Efficiency	90 %
Electrical data Output	
Output voltage DC	23 V
Output voltage DC min.	22,54 V
Output voltage DC max.	23,46 V
Output voltage adjustable	no
Output current max.	3 A
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Storage temperature min.	-20 °C
Storage temperature max.	60 °C
Conformity	
Product standard	EN 60950, EN 50178