

M12-DISTRIBUTOR BOX 4-WAY, 5-POLE WITHOUT LED

MVC4-UQQ5.0-XA 5m PUR-CNOMO-cable 8x0,34/3x1


4-way, 5-pole  
PUR/PVC (CNOMO)  
5.0 m  
without LED

Link to Product

Illustration



Product may differ from Image



取引条件

|                |               |
|----------------|---------------|
| ECLASS-6.0     | 27279219      |
| ECLASS-7.0     | 27279219      |
| ECLASS-8.0     | 27279219      |
| ECLASS-9.0     | 27440108      |
| ETIM-5.0       | EC002585      |
| GTIN           | 4048879000178 |
| HSコード          | 85444290      |
| Packaging unit | 1             |

Electrical data | Supply

|                                    |      |
|------------------------------------|------|
| Operating voltage DC               | 24 V |
| Current operating per contact max. | 4 A  |
| Total current max.                 | 10 A |

Industrial communication

|                            |   |
|----------------------------|---|
| Number of signals per port | 2 |
|----------------------------|---|

Installation | Connection

|              |         |
|--------------|---------|
| Mounting set | M12 x 1 |
|--------------|---------|

Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP67              |
| Additional condition protection degree | inserted, screwed |

Mechanical data | Mounting data

|                 |                |
|-----------------|----------------|
| Mounting method | Schraubgewinde |
| Height          | 117 mm         |
| Width           | 54 mm          |

Depth 33 mm

Environmental characteristics | Climatic

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -20 °C |
| Operating temperature max. | 80 °C  |

Connection type 2

|                          |                |
|--------------------------|----------------|
| Family construction form | free cable end |
| No. of poles             | 11             |
| Family construction form | M12            |
| Gender                   | female         |
| Color contact carrier    | black          |
| Coding                   | A              |
| No. of poles             | 5              |
| PIN 1                    | +              |
| PIN 3                    | -              |
| PIN 5                    | PE             |