

SCREW PLUG M12 STAINLESS STEEL

6-edges, 14 mm

Screw plug M12×1 mm
Metal, hex, 1 piece
Stainless steel 1.4305 (V2A)

Link to Product

Illustration



Product may differ from Image

取引条件	
ECLASS-6.0	23111190
ECLASS-6.1	23111190
ECLASS-7.0	23111190
ECLASS-8.0	23111190
ECLASS-9.0	23111190
ECLASS-10.1	23111190
ECLASS-11.1	23111102
ECLASS-12.0	23111102
ETIM-5.0	EC000032
GTIN	4048879333764
HSコード	73269098
Packaging unit	1

Installation Connection	
Tightening torque	0,6 Nm
Mounting set	M12 x 1

Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed

Mechanical data Material data	
Material housing	Stainless steel 1.4305 (V2A)

Mechanical data Mounting data	
Mounting method	inserted, screwed, Shaking protection

Environmental characteristics Climatic	
Operating temperature min.	-100 °C

Operating temperature max. 205 °C