



VALVE PLUG SUPPRESSOR FORM A - 18MM

RC and LED, 110VAC/DC/10VA/W

110 V AC/DC
RC + LED
Remove plug gasket when fitting adapter. Other LED colors on request.

Link to Product

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-8.0	27371013
ECLASS-9.0	27371013
ECLASS-10.1	27371013

ECLASS-11.1	27371013
ECLASS-12.0	27371013
ETIM-5.0	EC000197
GTIN	4048879012133
HSコード	85363010
Packaging unit	1
Electrical data	
Drop-out delay time max.	20 ms
Holding power max.	10 W
Electrical data Supply	
Cut-off peak voltage max.	250 V
Electrical data Input	
Input voltage AC min.	48 V
Input voltage AC max.	130 V
Input voltage DC min.	48 V
Input voltage DC max.	130 V
Diagnostics	
Status indication LED	yellow
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Coating contact	silver-plated
Color housing	black
Material housing	PA
Material contact	Bronze
Mechanical data Mounting data	
Height	37 mm
Width	45 mm
Depth	30 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Housing temperature max. (EN 61347-2-13)	130 °C