

MIRO TR 24VDC 20KHZ IN<1MA FK OPTO-COUPLER MODULE

IN: 30 VDC - OUT: 48 VDC / 0.2 A

Transistor 0.2 A
24 V DC
Control current 0.1 mA (5 V DC)
Spring clamp terminals

[Link to Product](#)

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27371601
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-8.0	27371604
ECLASS-9.0	27371604
ECLASS-10.1	27371604

ECLASS-11.1	27371604
ECLASS-12.0	27371604
ETIM-5.0	EC001504
GTIN	4048879021791
HSコード	85414900
Packaging unit	1
Electrical data Input	
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	2 V
Input voltage DC min.	15 V
Input voltage DC max.	30 V
Input current DC max.	16 mA
Control current	0,1 mA
Electrical data Output	
Switch off delay max.	18 µs
Quiescent current OFF max.	0,1 mA
Switching frequency max.	20000 Hz
Voltage switching DC min.	5 V
Switching voltage DC max.	48 V
Switching current min.	0,1 mA
Switching current max.	0,2 A
Voltage drop DC max.	1,2 V
Diagnostics	
Status indication LED	yellow
Device protection Electrical	
Rated insulation voltage	3750 V
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Color housing	black
Material housing	Plastic
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	91 mm
Width	6,2 mm
Depth	70 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Connection type 5	
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	-
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female

Color contact carrier	black
No. of poles	1
PIN 1	+
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	In
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	14
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	13