

MST 1-PHASE SAFETY TRANSFORMER

P: 320VA IN: 230/400VAC OUT: 24VAC

Single-phase safety transformer  
320 VA  
Spring clamp terminals  
Isolation class T 40/B  
Other voltages on request.

[Link to Product](#)

Illustration



Product may differ from Image



| 取引条件       |          |
|------------|----------|
| ECLASS-6.0 | 27031302 |
| ECLASS-6.1 | 27031302 |
| ECLASS-7.0 | 27031302 |
| ECLASS-8.0 | 27031302 |
| ECLASS-9.0 | 27031302 |

|                |               |
|----------------|---------------|
| ECLASS-10.1    | 27031302      |
| ECLASS-11.1    | 27031302      |
| ECLASS-12.0    | 27031302      |
| ETIM-5.0       | EC002486      |
| GTIN           | 4048879066181 |
| HSコード          | 85043180      |
| Packaging unit | 1             |

**Electrical data**

|                |      |
|----------------|------|
| Security level | SELV |
|----------------|------|

**Electrical data | Supply**

|                 |              |
|-----------------|--------------|
| Power frequency | 50 ... 60 Hz |
|-----------------|--------------|

**Electrical data | Input**

|                                          |        |
|------------------------------------------|--------|
| Input voltage 1 AC                       | 230 V  |
| Input voltage 2 AC                       | 400 V  |
| Input current at input voltage 1 AC      | 1,52 A |
| Input current at input voltage 2 AC      | 0,88 A |
| Inrush current at input voltage 1        | 17,5 A |
| Inrush current at input voltage 2        | 10,1 A |
| Short-circuit current at input voltage 1 | 28 A   |
| Short-circuit current at input voltage 2 | 16,1 A |

**Electrical data | Output**

|                           |        |
|---------------------------|--------|
| Output voltage AC         | 24 V   |
| Output voltage adjustable | no     |
| Power rating AC max.      | 320 VA |

**Device protection | Electrical**

|                                        |      |
|----------------------------------------|------|
| Insulation test voltage input - output | 4 kV |
|----------------------------------------|------|

**Mechanical data | Mounting data**

|                            |                        |
|----------------------------|------------------------|
| Suitable for mounting type | Schlüssellochauhängung |
| Mounting dimension a       | 74,4 mm                |
| Mounting dimension b       | 90 mm                  |
| Mounting dimension c       | 5,8 mm                 |
| Height                     | 92,2 mm                |
| Width                      | 120 mm                 |
| Depth                      | 122,4 mm               |
| Diameter bore              | 5,8 mm                 |
| Length bore                | 10 mm                  |

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -20 °C |
| Operating temperature max. | 40 °C  |
| Storage temperature min.   | -40 °C |
| Storage temperature max.   | 80 °C  |

**Conformity**

|                  |                                                 |
|------------------|-------------------------------------------------|
| Product standard | EN 61558-2-4, EN 61558-2-6, EN 62041 category 0 |
|------------------|-------------------------------------------------|

**Connection type 3**

|                          |                    |
|--------------------------|--------------------|
| Connection type 1        | Input              |
| Connection type 2        | Output             |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| No. of poles             | 3                  |
| PIN 2                    | 230 V              |

|                          |                    |
|--------------------------|--------------------|
| PIN 3                    | 400 V              |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| No. of poles             | 2                  |
| PIN 2                    | 24 V DC            |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | metallic           |
| No. of poles             | 1                  |
| PIN 1                    | PE                 |