


MIRO 6.2 pluggable Plug-in module Optocoupler

IN: 24 VDC - OUT: 24 VDC / 6 A


Transistor 6 A
24 V DC

Link to Product

Illustration



Product may differ from Image



取引条件

ECLASS-6.0	27371604
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-8.0	27371604
ECLASS-9.0	27371604
ECLASS-10.1	27371604
ECLASS-11.1	27371604
ECLASS-12.0	27371604
ETIM-5.0	EC001504
GTIN	4048879535175
HSコード	85414900
Packaging unit	1

Electrical data | Input

Input voltage DC	24 V
Input voltage DC min.	18 V
Input voltage DC max.	30 V
Input current	9 mA

Electrical data | Output

Switch off delay max.	31 µs
Forward voltage max.	240 mV
Switching frequency inductive max.	50 Hz
Switching frequency ohmic max.	500 Hz

Voltage switching DC min.	3 V
Switching voltage DC max.	30 V
Switching current min.	10 mA
Switching current max.	6 A

Diagnostics

Status indication LED	yellow
-----------------------	--------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Rated insulation voltage	50 V
Rated surge voltage	2,5 kV

Mechanical data | Mounting data

Mounting method	inserted
Height	15 mm
Width	5 mm
Depth	28 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	50 °C