

MODLINK MSDD SOCKET INSERT GERMANY

250VAC/16A with LED yellow

Germany (VDE) white  
Screw terminals  
LED (yellow)

Link to Product

Illustration



Product may differ from Image



| 取引条件                                     |               |
|------------------------------------------|---------------|
| ECLASS-6.0                               | 27189217      |
| ECLASS-6.1                               | 27189217      |
| ECLASS-7.0                               | 27189217      |
| ECLASS-8.0                               | 27189217      |
| ECLASS-9.0                               | 27182806      |
| ECLASS-10.1                              | 27182806      |
| ECLASS-11.1                              | 27182806      |
| ECLASS-12.0                              | 27182806      |
| ETIM-5.0                                 | EC000020      |
| GTIN                                     | 4048879038294 |
| HSコード                                    | 85366990      |
| Packaging unit                           | 1             |
| Mechanical data   Mounting data          |               |
| Height                                   | 88 mm         |
| Width                                    | 51 mm         |
| Depth                                    | 68 mm         |
| Environmental characteristics   Climatic |               |
| Storage temperature min.                 | -30 °C        |
| Storage temperature max.                 | 60 °C         |
| Germany (VDE)                            |               |
| Connection cross section max.            | 6 mm²         |

|                            |                    |
|----------------------------|--------------------|
| AWG number max.            | 10                 |
| Operating voltage AC       | 250 V              |
| Operating current          | 16 A               |
| Status indication LED      | yellow             |
| Connection                 | Screw terminals SK |
| No. of poles               | 2 + PE             |
| Connections per pole       | 2                  |
| Protection contact present | yes                |