

MODLINK MSDD SOCKET INSERT IEC

250VAC/10A acc. EN 60320-2-2/F

Appliance-outlet (IEC/EN 60320-2-2/F)
Spring clamp terminals: max. 2× 2.5 mm² (AWG 14)

Link to Product

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
GTIN	4048879038225
HSコード	85366990
Packaging unit	1
Mechanical data Mounting data	
Height	88 mm
Width	51 mm
Depth	30 mm
Environmental characteristics Climatic	
Storage temperature min.	-25 °C
Storage temperature max.	60 °C
Appliance-outlet	
Connection geometry	6.3 x 0.8 mm

Operating voltage AC	250 V
Operating current	10 A
Current operating ULc	15 A
Connection	plug-in connection
No. of poles	2 + PE
Protection contact present	yes