

MODLINK MSDD SOCKET INSERT AUSTRALIA

240VAC/15A

Australia
Screw terminals

[Link to Product](#)

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
GTIN	4048879038218
HSコード	85366990
Packaging unit	1
Mechanical data Mounting data	
Height	88 mm
Width	51 mm
Depth	35 mm
Environmental characteristics Climatic	
Storage temperature min.	-10 °C
Storage temperature max.	60 °C
Australia	
Connection cross section max.	4 mm²
AWG number max.	12

Operating voltage AC	240 V
Operating current	15 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes