

MODLINK MSDD DATA INSERT

1×RJ45 + 1×SUB-D9 blind

RJ45
1× RJ45, 8-pole metal, CAT5e (female/female)
1× SUB-D9 (blind plug)

Link to Product

Illustration



Product may differ from Image



取引条件

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
GTIN	4048879037617
HSコード	85366990
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	40 mm

Environmental characteristics | Climatic

Storage temperature min.	5 °C
Storage temperature max.	40 °C

RJ45

Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector