

EOL - SIGNAL TOWER MODLIGHT50 EQUIPPED WITH LED MODULES

Product discontinued

ベーシック、ブザー、フラッシュ + LED モジュール
緑, 黄, 赤

Link to Product

Illustration



Product may differ from Image

Technical Data	
Operating voltage	24 V DC (21.6...26.4 V DC)
Current consumption	max. 62.5 mA
Sound pressure level	70 ±5...90 ±5 dB
Blink cycles	毎分 60 ±12
General data	
Protection	IP65 ネジ締込時 (EN 60529)
Connection	ばね式端子台
Housing	プラスチック 黒
Dimensions H×W×D	293×50×50 mm
Temperature range	-30...+60 °C
取引条件	
GTIN	4048879322256
HSコード	85318070
Packaging unit	1