

Modlight50 Pro connecting modul base mounting

Input 24VDC

Base for floor mount
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



取引条件

ECLASS-6.0	27371232
ECLASS-6.1	27371232
ECLASS-7.0	27371232
ECLASS-8.0	27371232
ECLASS-9.0	27371232
ECLASS-10.1	27371232
ECLASS-11.1	27371232
ECLASS-12.0	27371232
ETIM-5.0	EC001152
ETIM-6.0	EC001152
ETIM-7.0	EC001152
GTIN	4048879751551
HSコード	85319000
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Color housing	black
Material housing	Plastic
Mechanical data Mounting data	
Height	180 mm
Width	50 mm
Depth	50 mm
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	60 °C
Connection type 1	
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	9
PIN 1	LED-Modul RD
PIN 2	LED-Modul YE
PIN 3	LED-Modul GN
PIN 4	LED-Modul BU
PIN 5	LED-Modul CL
PIN 6	Buzzer
PIN 7	24 V DC (0 V)
PIN 8	Blinking
PIN 9	0 V (24 V DC)