

**Modlight70 Pro LED modul red**

Input 24VDC

LED module (red)

[Link to Product](#)

Illustration



Product may differ from Image



取引条件

|                |               |
|----------------|---------------|
| ECLASS-6.0     | 27371200      |
| ECLASS-6.1     | 27371220      |
| ECLASS-7.0     | 27371220      |
| ECLASS-8.0     | 27371220      |
| ECLASS-9.0     | 27371220      |
| ECLASS-10.1    | 27371220      |
| ECLASS-11.1    | 27371220      |
| ECLASS-12.0    | 27371220      |
| ETIM-5.0       | EC000232      |
| GTIN           | 4048879752626 |
| HSコード          | 85319000      |
| Packaging unit | 1             |

Electrical data | Supply

|                           |         |
|---------------------------|---------|
| Operating voltage DC      | 24 V    |
| Operating voltage DC min. | 21,6 V  |
| Operating voltage DC max. | 26,4 V  |
| Current consumption max.  | 62,5 mA |

Device protection | Electrical

|                                        |                  |
|----------------------------------------|------------------|
| Degree of protection (EN IEC 60529)    | IP65             |
| Additional condition protection degree | inserted, locked |

Mechanical data | Material data

|                  |    |
|------------------|----|
| Material housing | PC |
|------------------|----|

Mechanical data | Mounting data

|                                          |                 |
|------------------------------------------|-----------------|
| Height                                   | 49 mm           |
| Width                                    | 70 mm           |
| Depth                                    | 70 mm           |
| Environmental characteristics   Climatic |                 |
| Operating temperature min.               | -30 °C          |
| Operating temperature max.               | 60 °C           |
| Connection type 1                        |                 |
| Mounting method                          | bayonet-locking |