

Signal tower Modlight70 Pro equipped with LED modules

blue,green,amber,red,buzzer

Basis, buzzer, LED modules
red, yellow, green, blue

Link to Product

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-8.0	27371230
ECLASS-9.0	27371230
ECLASS-10.1	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ETIM-5.0	EC001042
GTIN	4048879759915
HSコード	85318070
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	430 mA
Industrial communication HMI	
Buzzer sound	fast beep, continuous beep, fast high-low, sweep tone
Reduced sound pressure at 1 m	80 dB
Sound pressure at 1 m	90 dB
Device protection Electrical	

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked
Mechanical data Material data	
Color housing	black
Material housing	Plastic
Mechanical data Mounting data	
Height	334 mm
Width	70 mm
Depth	70 mm
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	60 °C