

M12 FEMALE 0°

PUR 3X0.34 GRAY, UL/CSA, drag ch 1.5m



M12 ,3

7005 - M12 Lite -


[Link to Product](#)

Illustration


stay connected



Female



Product may differ from Image



* UL/CSA

cCSAus

CE

EAC

Form

Form 12181

/ 3 x 0.34 mm²

C-track properties 10 Mio.

	PP (, ,)
	PUR (UL/CSA)
	4.1 mm ±5%
	10×
	-40...+80 °C
	-25...+80 °C
	233
	3 (PUR)
()	cRUus (AWM-Style 20549/10493); CE conform
[g/m]	29,70
()	max. 57 Ω/km (20 °C)
()	0.1 mm
()	42× 0.1 mm (6)
	3× 0.34 mm ²
AWG	AWG 22
	PP
	CFC
	70 ±5 D
	1.25 mm ±5%
/	
	3
	no
	PUR
)	CFC
Shore hardness (jacket)	90 ±5 A
()	4.1 mm ±5%
()	
	(EN 60811-404)
	300 V AC
	2500 V AC
	DIN VDE 0298-4
	-40 +80 (+90 10 000)
	-25 +80 (+90 10 000)
	5×
	10×
()	max. 10 Mio. (25 °C)
()	max. 3 m/s
()	max. 10 m/s ²
	±180°/m
	max. 2 Mio. (25 °C)
	35
	max. 250 V AC/DC
UL listed	max. 30 V AC/DC
	max. 4 A
	2.5 kV
	IEC 60664-1, category I
	3
	A

	(M12×1 mm) 0.6 Nm
	M12 (SW13)
	IP65, IP66K, IP67 EN 60529
	,
	PUR
()	10 mm
	DIN EN 61076-2-101 (M12)
	3
	,
	20 mm
	-25 +85 ,
EAN	4048879213974
eClass	27279218
HS	85444290
Packaging unit	1
	DE