




MODL.VARIO insert for fixed housing type B

B-code M12, male, shielded

Insert - stationary housing
Male straight – female straight
M12, 4-pole
B-coded
Good chemical and oil resistance (oil resistance does not apply to use with PVC cable)
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

Side 1	
Family construction form	M12
Coding	B
Material contact	Copper alloy
No. of poles	4
Side 2	
Family construction form	M12
Coding	B
Material contact	Copper alloy

No. of poles	4
取引条件	
ECLASS-6.0	27260702
ECLASS-6.1	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440106
ECLASS-10.1	27440106
ECLASS-11.1	27440106
ECLASS-12.0	27440106
ETIM-5.0	EC001855
GTIN	4048879576499
HSコード	85366990
Packaging unit	1
Electrical data Supply	
Operating voltage AC max.	49 V
Operating voltage DC max.	49 V
Current operating per contact max.	4 A
Installation Connection	
Tightening torque	0,6 Nm
Mounting set	M12 x 1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65, IP67
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	1,5 kV
Material group (IEC 60664-1)	I
Mechanical data	
Contour for corrugated hose	without
Mechanical data Material data	
Coating housing	nickel plated
Coating contact	gold plated
Material gasket	FKM
Material housing	Brass
Mechanical data Mounting data	
Mounting method	inserted, screwed, Shaking protection
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Conformity	
Product standard	DIN EN 61076-2-101 (M12)