

M8 panel feed through 3p shielded

制御キャビネット エントリーシステム
オス - メス
M8 ,3極
後方取り付け
シールド

[Link to Product](#)**Illustration**

Product may differ from Image

認証

Approvals

More Info

Bus technologies

Form

Form 88111

General data

Mounting method	inserted, tightened
Material (contact)	Copper alloy
Material (contact surface)	Au
Pollution Degree	3
Temperature range	-25...+85 °C
Material (contact carrier)	PA

Technical Data

Operating voltage	250 V
Rated surge voltage	2.5 kV
Operating current per contact	max. 4 A
No. of poles	3
Material group	3
Mating cycles	≥ 100
LED display	no
Compression gland	M8
Protection	IP67 inserted and tightened (EN 60529)
suitable for corrugated tube (internal Ø)	without
Housing	Metal
Over voltage category	2

取引条件

The information in this brochure has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 04/21

EAN	4048879689298
eClass	27143423
HSコード	85366990
Packaging unit	1.000
生産現国	DE