

Wall bushing for push pull power

With spring-cage connection, flexible coding


Push Pull Power metal mounting frame
incl. contact insert with spring clamp connection
flexible coding
Suitable for rectangular mounting cut-out
with gasket
without fixing screws

Link to Product

Illustration



Product may differ from Image



取引条件	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27440210
ECLASS-11.1	27440210
ECLASS-12.0	27440210
ETIM-5.0	EC002635
GTIN	4048879900454
HSコード	85366990
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Operating current	16 A
Installation	
Connection cross section min.	0,75 mm²
Connection cross section max.	2,5 mm²
AWG number min.	18

AWG number max. 13

Installation | Connection

Connection	Spring clamp terminals FK
Mating cycles min.	100

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65, IP67
Additional condition protection degree	inserted, screwed
Pollution Degree	2
Rated surge voltage	4 kV

Mechanical data | Material data

Coating housing	nickel plated
Combustibility class (UL94)	V-0
Material housing	Zinc die-casting

Mechanical data | Mounting data

Mounting method	5-pole, PPP
-----------------	-------------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	70 °C