

M12 FEMALE 0° V2A

PUR 5X0.34 YELLOW, UL/CSA, drag ch 10m

M12, 5



7005 - M12 Lite -

1.4305 V2A

[Link to Product](#)


Illustration

stay connected




(* for cable type 126, 732, 219, 619)

Female



Product may differ from Image



* UL/CSA

Form

Form 12241

/ 5x 0.34 mm²

	PP (, , , ,)
C-track properties	10 Mio.
	PUR (UL/CSA)
	4.8 mm ±5%
	10×
	-40...+80 °C
	-25...+80 °C
	035
	3 (PUR)
()	cRUus (AWM-Style 20549/10493); CE conform
[g/m]	41,80
()	max. 57 Ω/km (20 °C)
()	0.1 mm
()	42× 0.1 mm (6)
	5× 0.34 mm ²
AWG	AWG 22
	PP
	CFC
	70 ±5 D
	1.25 mm ±5%
/	
	5
	no
	PUR
)	CFC
Shore hardness (jacket)	90 ±5 A
()	4.8 mm ±5%
()	
	(EN 60811-404)
	300 V AC
	2500 V AC
	DIN VDE 0298-4
	-40 +80 (+90 10 000)
	-25 +80 (+90 10 000)
	5×
	10×
()	max. 10 Mio. (25 °C)
()	max. 3 m/s
()	max. 10 m/s ²
	±180°/m
	max. 2 Mio. (25 °C)
	35
	max. 125 V AC/DC
UL listed	max. 30 V AC/DC
	max. 4 A
	IEC 60664-1, category I
	A

	(M12×1 mm) 0.6 Nm
	M12 (SW13)
	IP66K, IP67 EN 60529
	1.4305 V2A
	PUR
()	10 mm
	DIN EN 61076-2-101 (M12)
	3
	-25 +85 ,
EAN	4048879372718
eClass	27279218
HS	85444290
Packaging unit	1
	DE