

**M12 FEMALE 90° V2A**

PUR 4X0.34 black UL/CSA, drag ch 10m

90°

M12, 4




7005 - M12 Lite -

1.4305 V2A


[Link to Product](#)

Illustration

*stay connected*



Female



Product may differ from Image



\* UL/CSA

Form	
Form	12341
/	4 × 0.34 mm <sup>2</sup>
	PP ( , , , )
C-track properties	10 Mio.
	PUR (UL/CSA)
	4.5 mm ±5%
	10×
	-40...+80 °C
	-25...+80 °C
	634
	3 (PUR)
( )	cRUus (AWM-Style 20549/10493); CE conform
[g/m]	36,30
( )	max. 57 Ω/km (20 °C)
( )	0.1 mm
( )	42 × 0.1 mm ( 6)
	4 × 0.34 mm <sup>2</sup>
AWG	AWG 22
	PP
	CFC
	70 ±5 D
	1.25 mm ±5%
/	4
	no
	PUR
)	CFC
Shore hardness (jacket)	90 ±5 A
( )	4.5 mm ±5%
( )	(EN 60811-404)
	300 V AC
	2500 V AC
	DIN VDE 0298-4
	-40 +80 (+90 10 000 )
	-25 +80 (+90 10 000 )
	5×
	10×
( )	max. 10 Mio. (25 °C)
( )	max. 3 m/s
( )	max. 10 m/s <sup>2</sup>
	±180°/m
	max. 2 Mio. (25 °C)

35

	max. 250 V AC/DC
UL listed	max. 30 V AC/DC
	max. 4 A
	IEC 60664-1, category I
	(M12×1 mm) 0.6 Nm
	M12 (SW13)
	IP66K, IP67 EN 60529
	1.4305 V2A
	PUR
( )	10 mm
	DIN EN 61076-2-101 (M12)
	3
	-25 +85 ,
EAN	4048879112307
eClass	27279218
HS	85444290
Packaging unit	1
	DE