

1,6 mm crimp contact m/turned/gold 0,14-0,37 mm²

100 Stück

Turned crimp contact
Male
1.6 mm
0.14...0.37 mm² (AWG 26...22)
Quantity: 100 pcs.
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

取引条件	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
GTIN	4048879649933
HSコード	85366990
Packaging unit	100
Installation	
Connection cross section min.	0,14 mm²
Connection cross section max.	0,37 mm²
AWG number min.	26
AWG number max.	22
Installation Connection	
Stripping length	7 mm
Connection	Crimp
Gender	male
Mating cycles min.	500
Mechanical data Material data	

Coating contact	gold plated
Material contact	Brass
Mechanical data Mounting data	
Height	3,2 mm
Width	3,2 mm
Depth	25 mm