

MODL. VARIO 10-way coupling housing type B

stainless steel type 1.4404 (V4A)

Mobile housing
Stainless steel 1.4404 (V4A)
10-way

Link to Product

Illustration



Product may differ from Image

取引条件	
ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
GTIN	4048879573177
HSコード	85389099
Packaging unit	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed
Mechanical data	
Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar
Mechanical data Material data	
Material housing	Stainless steel 1.4404 (V4A)
Mechanical data Mounting data	
Mounting method	screw fixing
Environmental characteristics Climatic	
Operating temperature min.	-20 °C

Operating temperature max. 120 °C