

MODL.VARIO Accessories closure plug 4/2

for adaptive inserts, nickel plated brass

Modlink Vario
Accessories
Locking plug
Diameter
4 mm
Quantity: 10 pcs.
good resistance to oil, gasoline and chemicals
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

取引条件	
ECLASS-6.0	27260702
ECLASS-6.1	27269202
ECLASS-7.0	27449203
ECLASS-8.0	27449203
ECLASS-9.0	27440192
ECLASS-10.1	27440192
ECLASS-11.1	27440192
ECLASS-12.0	27440192
ETIM-5.0	EC002641
GTIN	4048879618878
HSコード	85389099
Packaging unit	10
Mechanical data	
Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar
Mechanical data Material data	
Coating housing	nickel plated
Material housing	Brass
Mechanical data Mounting data	
Size	AD4
Height	19 mm

Width	5,5 mm
Depth	5,5 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	120 °C