

MODL. VARIO insert for fixed housing type B

8/6 no shut-off, dezincification resistant brass

Modlink Vario
Insert - stationary housing
Brass, dezincification-resistant
without shut-off
AD8

Link to Product

Illustration



Product may differ from Image

取引条件	
ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
GTIN	4048879572552
HSコード	74198090
Packaging unit	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed
Mechanical data	
Barrier	without shut-off
Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar
Mechanical data Material data	
Material gasket	FPM
Material housing	Brass
Mechanical data Mounting data	

Outer diameter hose	8 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	120 °C