

MODL.VARIO Accessories hose bundle D2=42

for coupling housing, nickel plated aluminium, FPM

Hose bundling
good resistance to oil, gasoline and chemicals
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

取引条件	
ECLASS-6.0	27260702
ECLASS-6.1	27269202
ECLASS-7.0	27449203
ECLASS-8.0	27449203
ECLASS-9.0	27440192
ECLASS-10.1	27440192
ECLASS-11.1	27440192
ECLASS-12.0	27440192
ETIM-5.0	EC002641
GTIN	4048879614344
HSコード	76169990
Packaging unit	1
Mechanical data Mounting data	
Height	48 mm
Width	80 mm
Depth	48 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	120 °C