MURR ELEKTRONIK
stay connected

SUPPRESSOR FOR CONTACTORS


RC, 400 VAC/DC 50 VA/W


400 V AC/DC
RC
For other configurations and voltages, please inquire.

[Link to Product]

Illustration







Product may differ from Image

Commercial data

ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-8.0	27371013
ECLASS-9.0	27371013
ECLASS-10.1	27371013

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

ECLASS-11.1	27371013
ECLASS-12.0	27371013
ETIM-5.0	EC002498
customs tariff number	85363010
GTIN	4048879020305
Packaging unit	1
Compatibility | Compatible with	
Appropriate contactors	universal
Electrical data	
Damping factor	1.5× UN
Holding power max.	50 W
Electrical data | Input	
Input voltage AC min.	240 V
Input voltage AC max.	400 V
Input voltage DC min.	240 V
Input voltage DC max.	400 V
Installation | Connection	
Connection information	flexible connection wires
Device protection | Media	
Flame resistance	flame retardant
Mechanical data | Material data	
Combustibility class housing (UL94)	V-0
Material housing	Plastic
Mechanical data | Mounting data	
Height	22 mm
Width	27 mm
Depth	11 mm
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	70 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28