
POTENTIAL TERMINAL BLOCK GRAY GRAY BR BL

Potential terminal block
gray/gray/brown/blue

Link to Product

Illustration





Product may differ from Image

Commercial data

ECLASS-6.0	27141106
ECLASS-6.1	27141106
ECLASS-7.0	27141106
ECLASS-8.0	27141106
ECLASS-9.0	27141106
ECLASS-10.1	27141106
ECLASS-11.1	27141106
ECLASS-12.0	27141106
ETIM-5.0	EC001283
customs tariff number	85369010
GTIN	4048879049467
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	30 V
Operating voltage DC max.	30 V
Total current max.	10 A

Installation

Connection cross section max.	2,5 mm²
AWG number min.	28
AWG number max.	14

Installation | Connection

Connection	Spring clamp plug-in terminals

Device protection | Electrical

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

Degree of protection (EN IEC 60529)	IP20
Mechanical data | Mounting data	
Height	70 mm
Width	56 mm
Depth	32,5 mm
Environmental characteristics | Climatic	
Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28