MURR ELEKTRONIK
stay connected

EUROCARD HOLDER


SKP 24/7


Screw terminals
24-, 7-pole M (EN 60603)
Row z, b, d
With the vertical snap adapter SASA 135 Art.-No. 63900 the holder can be mounted at right-angles on the rail.
The D2 size is for a card without a front plate.
To insert the card first press down the 2 yellow buttons. Then slide the Eurocard into the guide slots pushing until fully engaged. The card is now locked into position. It can be removed by pressing down on the 2 yellow buttons.

Link to Product

Illustration







Product may differ from Image

Side 1

Operating voltage AC	500 V
Operating current max.	4 A
No. of poles	7

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

MURR ELEKTRONIK
stay connected

Side 2	
Operating voltage AC	250 V
Operating current max.	15 A
No. of poles	24
Commercial data	
ECLASS-6.0	27260710
ECLASS-6.1	27260704
ECLASS-7.0	27440402
ECLASS-8.0	27440402
ECLASS-9.0	27460201
ECLASS-10.1	27440402
ECLASS-11.1	27460201
ECLASS-12.0	27460201
ETIM-5.0	EC002780
customs tariff number	85366990
GTIN	4048879042079
Packaging unit	1
Installation	
Connection cross-section solid max.	4 mm²
Installation | **Pin assignment**	
No. of poles	24 + 7
Device protection | **Electrical**	
Overvoltage category (EN 60664-1)	I
Device protection | **Media**	
Flame resistance	flame retardant
Mechanical data	
Type of socket connector	M (EN 60603)
Mechanical data | **Material data**	
Material housing	Plastic
Mechanical data | **Mounting data**	
Mounting method	screwed, geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	137 mm
Width	63 mm
Depth	170 mm

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28